
METAPOR[®] - BF 100 AL Air Permeable Material


Technical Bulletin



Tooling Technology, LLC.
100 Enterprise Drive
Fort Loramie, OH 45845
TEL (937) 295-3672 FAX - 3677
email: jbarker@toolingtechgroup.com
www.segen-online.com

General

METAPOR[®] is a composite material made of aluminum granules and epoxy resin. The material is air-permeable over the entire surface due to its micro-porous structure allowing for unique design considerations for prototype and production thermoform tools. In contrast to sintered materials, the pores do not close off after machining allowing excellent definition and surface quality.



Thermoformers have seen some of the following advantages:

- High Definition and Accuracy
- Faster Air Evacuation
- Improved Surface Quality
- Reduced Machine Time
- Trapped Air Elimination
- Improved Mold Detail

METAPOR[®] - BF 100 AL

METAPOR[®] - BF 100 AL is the standard grade and can be used with polymer sheet most commonly thermoformed today such as PS, ABS, PVC, PET and PE. Its upper operating temperature limit is 212 °F (100 °C).

Physical properties at 67°F (20 °C)

Property	Value (Eng)	Value (SI)
Density	112.3 lb/ft ³	1.8 g/cm ³
Hardness Shore D	81	81
Flexural strength	8,126 psi	56 N/mm ²
Flexural Modulus	1,306 ksi	9000 N/mm ²
Impact strength	1.23 BTU/ft ²	14 kJ/m ²
Coefficient of thermal expansion 25 °C -125°C (77 - 257 °F)	16.7 x 10 ⁻⁶ in/in/°F	30.4 x 10 ⁻⁶ mm/mm/°C
Thermal conductivity: at 100°C (212 °F)	10.3 BTU/ hr-ft-°F	19.1 W / m-°C
Martens Dimensional Stability	226 °F	108 °C
Mean pore diameter	.0006 in	15 μm
Total porosity (by volume)	15 %	15 %

METAPOR - BF 100 AL

Tooling Technology, LLC (937) 295 - 3672

Design and Handling

For detailed information on Handling, Machining and Adhesive bonding of METAPOR[®], please refer to the "Handling Guidelines" brochure.

Storage

Store dry, protect against jolts and impacts. Avoid contact with grease and fluids.

Machining

The machining properties of METAPOR[®] are excellent and are comparable with rapid machinable aluminium. **METAPOR[®] must be machined dry and should not be in contact with any cooling liquids.** In order to avoid any closure of pores, sharp tools made of HSS or carbide with edge angles as for aluminium must be used. It is recommended to use dust extraction. Avoid contact with grease and fluids

Cutting speed up to 3300 ft/min can be applied. The forward feed can be set up to 0.004 in/ tooth; in areas of thin walls the forward feed should be reduced.

Grinding/Polishing

Grinding and polishing of the machined surfaces can be made by hand or with a vibrating grinder. Use corundum paper with grains of 400 / 600 / 1200 in the ascending order. **METAPOR[®] has to be polished dry and without any polishing paste!**

Air Flow Rates

The numbers are average values for calculating air consumption for overpressure or underpressure applications. Specification is in cubic inches per minute per in².

Pressure difference in nsi	Plate thickness in Inches							
	0.39	0.59	0.79	0.98	1.18	1.57	2.36	3.94
2.9	153.4	125.9	110.1	94.4	82.6	66.9	39.3	7.9
4.4	184.9	153.4	133.7	118.0	106.2	86.5	55.1	19.7
5.8	216.3	184.9	161.3	141.6	125.9	102.3	70.8	27.5
7.3	247.8	208.4	184.9	165.2	149.5	121.9	86.5	39.3
8.7	279.2	236.0	208.4	184.9	169.1	141.6	98.3	47.2
10.2	306.8	263.5	232.0	208.4	188.8	157.3	114.1	59.0
11.6	338.2	291.0	255.6	232.0	208.4	177.0	129.8	66.9
13.1	369.7	318.6	279.2	251.7	228.1	192.7	141.6	78.7
14.5	397.2	342.2	302.8	275.3	251.7	212.4	157.3	86.5
29.0	676.5	590.0	527.0	479.8	440.5	377.6	291.0	180.9
43.5	920.3	806.3	723.7	660.7	609.6	527.0	413.0	267.4
58.0	1132.7	995.0	896.7	822.0	759.1	660.7	523.1	350.0
72.5	1313.6	1156.3	1046.2	959.7	888.9	778.7	621.4	424.8
87.0	1459.1	1290.0	1168.1	1077.6	999.0	881.0	707.9	495.6

Available Sizes

METAPOR[®] is manufactured in blocks of 500 x 500 x 400 mm, (~20" x 20" x 16"), and cut into slabs of any required thickness. After the cutting process, the air permeability of the slab surface is reduced due to partial closure of the pores. It is essential to **mill both surfaces of the slab** by cutting off approx. 0.5 mm, (0.02"), providing complete air permeability.